

For Converting

- Strip & Island Dressings
- Hydrogel Dressings
- Hydrocolloid Dressings
- Breathable Polyurethane
- Electrodes
- Combination Alginates



Benefits

- Up to 400 products/minute
- Multiple dressing sizes & formats
- Electronic web tensioning and web guiding minimize waste levels
- Automatic inspection and reject system ensures consistent quality
- Fully validated, GMP, CE and OSHA compliant
- Auto-splicing for quick reel changeover and continuous motion production optional
- Integration with Four Side Seal Packaging Machine possible for continuous converting and packaging, optional ancillary equipment like collators, feeders and bulk roll handling systems increase convenience, efficiency and personnel safety while reducing downtime and product damage.

Doyen's DMS system is a flexible solution for Traditional and Advanced Wound Care converting.


Dressing Converting System - DMS

TECHNICAL INFORMATION



The release liner is unwound and applied to the dressing.

Reel diameter sensors ensure efficient material handling.



Process Direction →

Model	DMS
Web width	up to 250mm
Product length	up to 300mm
Web speed	up to 50m / minute
Dimensions (ca.)	L 7m x W 1.6m x H 2m

Doyen Medipharm Ltd
 Gateway 11 Business Park, Copper Smith Way,
 Wymondham, Norfolk, NR18 0WY, UK
 Tel: (+44) 01953 600078 - Fax: (+44) 01953 605069
 sales@doyenmedipharm.co.uk

Doyen Medipharm LLC
 4030 South Pipkin Road, Suite 102,
 Lakeland, Florida 33811, USA
 Tel: (+1) 863-683-6335 - Fax: (+1) 863-683-6857
 salesUS@doyenmedipharm.com

Doyen Medipharm Ltd
 5008 Jalan Lunas, First Floor, Batu 2 1/2
 Kulim, Kedah Darul Aman, Malaysia
 Tel: (+604) 495 1619 - Fax: (+604) 495 1697
 Surren@DoyenMY.com

Europe
 North and South America
 Asia



www.doyenmedipharm.com